



## Electronic Exposed Battery Urinal Flush Valve with Mechanical Manual Override

### **81T231BTA-MMO**

#### **Description**

Electronic exposed battery flush valve with MMO (mechanical manual override) for 0.75" (19 mm) top spud urinal fixture with quiet action chloramine-resistant diaphragm and adjustable flush volume factory set to 0.5 gpf (1.9 Lpf).

#### **Specification**

- Flush Volume: Adjustable factory set @ 0.5 gpf (1.9 Lpf)
- Fixture Type: Urinal with 0.75" (19 mm) top spud
- · Valve Type: Urinal Flush Valve
- Operation: H<sub>2</sub>Optics<sup>®</sup> sensing technology

#### **Features**

- Polished chrome-plated vandal resistant metal cover with top mounted sensor operated H<sub>2</sub>Optics<sup>®</sup> electronics
- · Right or left-hand supply installation
- · True mechanical manual override button
- · ADA compliant, automatic operation battery powered infrared sensor
- · Scratch resistant replaceable lens window
- Four (4) size AA alkaline batteries factory installed with valve in sleep mode for easy installation
- · Hinged battery housing for easy maintenance
- Quiet action, TECK® exposed diaphragm flush valve
- · Chloramine resistant diaphragm
- · Renewable seat
- Polished chrome-plated finish for an attractive and corrosion-resistant appearance
- · Maximum 13" (330 mm) from centerline of valve inlet to top of water closet
- 1.0" (25 mm) FIP / 0.75" (19 mm) Copper Sweat inlet adaptor, angle check stop with protecting cap
- Adjustable 4.75" ±0.5" (121 mm ±13 mm) inlet/valve outlet centers
- Vacuum breaker
- Cover tube, stainless steel wall flange, spud flange, spud nut, and 13" (330 mm) outlet tube
- Water conserving adjustable flush volume from 0.125 1.0 gpf (0.47 3.78 Lpf) and factory set to 0.5 gpf (1.9 Lpf) for efficient water usage

#### **Optional Accessories**

- 061391A Copper Defense conversion kits with CuVerro Shield bactericidal copper alloys for 81T electronic flush valve button (Available in Canada Only)
- 061069A Hardwire converter & rigid connection assembly for 3rd Generation E-FV
- 060704A Transformer 20VA, 120/24Vac (for use with up to 5 units)
- 060771A Transformer 40VA, 120/24Vac (for use with up to 10 units)
- 061428A Standard left-hand thread tail 1" (25 mm) extension
- 061429A Standard left-hand thread tail 2" (51 mm) extension



#### **Complies With**

- ASSE 1037/ASME A112.1037/ CSA B125.37
- ICC / ANSI A117.1



(Contact Delta Representative for State and/or Local Approvals)

#### **Operation**


- Infrared sensor range adjustment to accommodate bowl length of 20 28" (508 - 711 mm), factory set at 24" ±2" (610 mm ±51 mm)
- Low battery flashing light (5000 flushes remaining) with battery strength indicator
- · Optional 24 hour automatic flush factory set to off
- · Set-up sensor range adjustment indicator lights
- · 6 VDC input, 6 second arming delay
- Electronic operated non-hold-open metal override button with 5 second lockout
- Recommended water supply:
  Minimum flowing pressure 25 psi (172 kPa)
  Minimum flow rate 8 gpm (30 L/min)






# Electronic Exposed Battery Urinal Flush Valve with Mechanical Manual Override

## **81T231BTA-MMO**





Teck® flush valves are designed to operate at any supply pressure between 20 psi and 125 psi in accordance with ASSE 1037/ASME AI 12.1037/ CSA BI25.37. The Teck® flush valve delivers the industry's highest peak flows to enhance bowl scrubbing. At high water pressures, splash out, noise or reduced life of plumbing components may be observed with a few models of water closet or urinal fixtures. To minimize or eliminate these effects, select a different model of water closet or urinal from the same or another manufacturer, or install a pressure reducing valve. If the installation does not allow for either of these options, the control stop adjusting screw may be used to reduce pressure to the valve.

NOTICE Dimensions are for reference only, measurements may vary  $\pm$  0.25" (6 mm). Maximum flow rates - 60 psi (414 kPa).

© 2025 Masco Canada Limited 350 South Edgeware Rd, St Thomas, Ontario, Canada N5P 4L1 1-800-387-8277