



Installation Instructions **LKQD35 Series LKQS35 Series**

LKQD35 - DISPOSAL FLANGE FITTING WITH REMOVABLE STRAINER FOR GARBAGE DISPOSALS




SINK

- (1) MAKE SURE DISPOSER IS INSTALLED PROPERLY TO SINK AND CLAMP IS SECURED
- CLEAN INSIDE OF METAL COLLAR (SUPPLIED WITH GARBAGE DISPOSER)



LUBRICATE FLANGE GASKET WITH WATER AND PUSH FLANGE SLOWLY INTO THE METAL COLLAR. PRESS FIRMLY UNTIL IN PLACE.




(4) LUBRICATE GASKET ON STRAINER WITH WATER AND PUSH SLOWLY INTO THE FLANGE

DESIGNED FOR GARBAGE DISPOSALS THAT ACCOMMODATE 3-1/2" (89mm) DIAMETER FLANGE, OR ANY DISPOSER WITH AN INSINKERATOR QUICK LOCK MOUNTING COLLAR EXCEPT THE INSINKERATOR EVOLUTION LINE. NOT INTENDED FOR THE FOLLOWING BRANDS: GE, SINKMASTER, WHIRLAWAY MODELS WITH THE EZ MOUNT FLANGE. NOT INTENDED TO FIT BATCH FEED GARBAGE DISPOSALS.

LIMITED 1 YEAR WARRANTY


- DRAINS ARE WARRANTED TO BE FREE FROM DEFECTS IN MATERIALS AND WORKMANSHIP FOR A PERIOD OF 1 YEAR FROM DATE OF PURCHASE.
- OUR WARRANTY DOES NOT COVER PRODUCT FAILURE OR DAMAGE CAUSED BY ABUSIVE TREATMENT, MISUSE, ENVIRONMENTAL FACTORS OR IMPROPER CARE AND CLEANING.
- NO ADDITIONAL WARRANTIES, EXPRESS OR IMPLIED ARE GIVEN.
- · THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MIGHT HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.
- PROOF OF PURCHASE INCLUDING DATE OF PURCHASE IS REQUIRED

LKQS35 - DRAIN WITH REMOVABLE **STRAINER**




(1) APPLY A SMALL AMOUNT OF NEUTRAL CURE* SILICONE CAULK / ADHESIVE UNDER THE RIM OF STRAINER FLANGE


(2) PLACE INTO SINK



3) LUBRICATE FLANGE GASKET WITH WATER, PLACE INTO LIP OF DRAIN BODY AND POSITION DRAIN BODY ON THE SINK **BOTTOM**



(4) LINE UP RIBS IN DRAIN BODY AND STRAINER FLANGE THEN SCREW IN FERRULE. CAUTION: HAND TIGHTEN THEN 1/4 TURN WITH SMALL SCREW DRIVER. DO NOT OVER TIGHTEN. REMOVE EXCESS CAULK / **ADHESIVE**



PUSH STRAINER INTO FERRULE IN DRAIN BODY

MAKER SURE WASHER IS IN POSITION, SLIDE NUT ON 1 1/2" DRAIN TUBING AND HAND TIGHTEN THE DRAIN BODY NUT. TEST FOR LEAKS.

*SOME EXAMPLES OF NEUTRAL CURE SEALANT ARE AS FOLLOWS:

- -GE SILICONE II PRODUCTS
- -WHITE LIGHTNING SILICONE ULTRA KITCHEN AND BATH
- -DAP SILICONE PRODUCTS

For Customer Care Support, Call: 800-476-4106