

Ensemble™

32" Whirlpool Bath **76121120**





Features

- Right drain.
- Integral apron with removable access panel.
- Durable high-gloss finish.
- 18" (457 mm) bath whirlpool depth (floor to top of threshold).
- 60-1/4" (1530 mm) x 33-1/4" (845 mm) x 75-1/4 (1911 mm) complete unit rough-in dimensions include flange.
- 60" (1524 mm) x 32" (813 mm) x 74" (1880 mm) complete unit finished dimensions.

Material

Compression-molded from our exclusive solid Vikrell® material.

Hydrotherapy

- Eight fully-adjustable hydro-massage jets (color-matched and factory-installed).
- Pump with air switch and grounding-type plug-in cord.

Installation

Alcove



ADA

Codes/Standards

ASME A112.19.7/CSA B45.10 CSA B45.5/IAPMO Z124 ASTM E162 ASTM E662 UL 1795 Greenguard UL 2818 - Gold ADA ICC/ANSI A117.1 CARB P2

STERLING® Warranty - Fixtures Made of Solid Vikrell Material

See website for detailed warranty information.

Available Color/Finishes


Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Riscuit



Ensemble™

32" Whirlpool Bath **76121120**



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Installation:

3-Wall Alcove

Drain location: Right

Basin area, bottom: 42" x 20" (1067 mm x 508 mm) Basin area, top: 54" x 26" (1372 mm x 660 mm)

Water depth: 13-3/4" (349 mm) Water capacity: 55 gal (208.2 L)

Electrical component Pump: 120 V, 7 A, 60 Hz

rating:

Pump speed: Single Minimum flat for door: 0" (0 mm)

Door width required: 57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

Measure your actual product for roughing-in details.

Pump is supplied with 24" (610 mm) grounding-type plug-in cord.

Locate the outlet behind the whirlpool, and within 24" (610 mm) of the pump.

Do not disassemble the pump or piping as this could void the warranty.

Size the drain cutout to fit the drain assembly that will be used.

ADA compliant when installed to the specific requirements of these regulations.